

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [M Series](#) / [M12 \[A\]](#)

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 [A]
- M12 [B]
- M12 [D]
- M12 [I]
- M12 [K]
- M12 [L]
- M12 [S]
- M12 [T]
- M12 [X]
- M23
- FL0S & FL0S+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



MSAP05ML-SAPFL-SD005

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: PVC
- Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

- 1 +

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



M Series, Accessory,...
CAP-WBDFMA1
-40°C ~ +105°C

- 0 +

☐



M Series, Accessory,...
CAP-WBDMMA1
-40°C ~ +105°C

- 0 +

☐



M Series, M12, A Code,...
M12A-05PFFR-EE0001
-40°C ~ +105°C

- 0 +

☐



M Series, M12, A Code,...
MSAP-05BFFA-SL8001
-40°C ~ +105°C

- 0 +

☐

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 4A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Straight
Mating Style Screw Thread	IP Rating IPX8
Assembly Style N/A	
 More Options	

People Also Bought

- 

MSAP05ML-...
- 

MSAP05FL-...
- 

FLKB-D4FGMS-...
- 

UMC-000505-...
- 

BD-D48FMA-...