



Part Number : 1300088079
Product Description : Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length
Series Number : 130008
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 303000B80M050



Documents & Resources

Drawings
[1300088079_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	889056891035

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	300V

Physical

Cable Diameter	10.20mm (.402")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold

Net Weight	798.700/g
Orientation	Straight to Pigtail
Poles	19
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	19, 22

This document was generated on Apr 26, 2025