

3500 00350003

[Products](#) > [Sensors](#) > [Humidity, Thermal & Flexible Heater Products](#) > [Thermostats/Thermal Switches](#) > [High Reliability](#) > [Military/Commercial Aircraft](#) > [3500 Series](#) > **3500 00350003**

Overview

3500 Series Military Thermostats.
The 3500 Series consists of a single pole, single throw switch activated by a snap action bimetal disc. Temperature calibrations are pre-set at the factory.
[View More](#)



[email sales](#)[view all products](#)[sample request](#)[distributor inventory](#)[find a distributor](#)[get support](#)

Technical Specifications

Functional Properties	Open on rise	Reset Type	Automatic
Operating Temperature	-51 °C to 204 °C [-60 °F to 400 °F]	Amperage	2.0 A/5.0 A
Voltage	115 Vac/28 Vdc	Open Temperature	260.0 °C [500 °F]
Open Tolerance	8.3 °C [15 °F]	Close Temperature	237.8 °C [460 °F]
Close Tolerance	8.3 °C [15 °F]	Environmental Exposure Range	-65 °C to 260 °C [-85 °F to 500 °F]

[View More](#)

Documents

View documents in:

English ▾

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
Precision and High Reliability Thermostats	Datasheet	--	4MB
Thermostats Line Guide	Product Line Guide	English	444KB
Soldering Wire Leads on Precision Hermetic Thermostats	Installation Instructions	English	57KB
Thermal Sensors	Product Range Guide	English	2MB

[View More](#)

Product Features

- Hermetically sealed
- Tight tolerances
- Tight differentials
- Hi-Rel

Applications

- Military and commercial aircraft

PRODUCTS

DISTRIBUTOR INVENTORY

INDUSTRIES

SUPPORT

NEWS & EVENTS

ABOUT US

AD PORTAL LOGIN / REQUEST
ACCESS

LEARN CENTER

SAMPLE REQUEST

SUPPLIER MICROSITE

SOCIAL MEDIA



SITE INFORMATION

PRIVACY STATEMENT

SITEMAP

TERMS & CONDITIONS

COPYRIGHT © 2019 HONEYWELL
INTERNATIONAL INC.