Part Number : 1553210001
Product Description : Flamar Power Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 1.50mm² with Green-Yellow Ground / 16 AWG with Green-Yellow Ground, 9.00mm (.354") Diameter, 200.0m (656.17') Length, Orange
Series Number : 307965
Status : Active
Product Category : Industrial Cable
Engineering Part Number : 1X200M



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable
Series	307965
Description	Flamar Power Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 1.50mm^2 with Green-Yellow Ground / 16 AWG with Green-Yellow Ground, 9.00mm (.354") Diameter, 200.0m (656.17') Length, Orange
Geographic Area	Global
Product Name	Flamar,Servo Motor
UPC	889056460330

Agency

UL	E172949

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V

Physical

Bending Radius - Minimum	> 10xOD
Cable Length	200.0m
Circuits (Loaded)	4
Color - Cable Jacket	Orange
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.132/kg
Outer Jacket Diameter	9.00mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C

Downloaded from Arrow.com.

Wire/Cable Type	UL AWM 21939 / CSA
Wire Size (AWG)	16
Wire Size mm^2	1.50

Mates With / Use With

Use with Part(s)

Description	Part Number
Brad M23 Signal Connectors	120230
Brad M23 Signal Connectors	120233

Downloaded from Arrow.com.