

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0795405015

Status:

Active

Overview:

In-Vehicle Smart Charging Modules

Description:

In-Vehicle Single Port USB Battery Charger with Backlight, 1.0A



Documents:	
3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)
Drawing (PDF)	
General	
Product Family	I/O Connectors
Series	79540
Application	Module-to-Wire
Component Type	USB Charger
Overview	In-Vehicle Smart Charging Modules
Product Name	Micro-Fit 3.0, USB
Type	A
UPC	887191430973
Physical	
Circuits (Loaded)	3
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	5000
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	ABS, PC
Net Weight	23.200/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	16V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-79540-5015-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Compliant with Exemption 7(c)-I,7(a)*	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)*	
Halogen-Free Status	
Not Low-Halogen*	
For more information, please visit Contact US	
CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from
CUST_NOTE2	product compliance status evaluation.
China ROHS	50 Image
ELV	Not Reviewed
RoHS Phthalates	Not Contained*

Search Parts in this Series

79540 Series

Mates With

USB Type A (Front)
Micro-Fit 3.0 Receptacle 436450500 (Rear)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION