
**Part Number :** 5024430970
**Product Description :** 2.00mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, 9 Circuits
**Series Number :** 502443
**Status :** Active
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

5024430970_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

AS-502439-001-001.pdf

AS-502439-002-001.pdf

5024439200-200.pdf

5024431570-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 34; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |

Downloaded from Arrow.com.

| | |
|---|---|
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 502443 |
| Description | 2.00mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Vertical, 9 Circuits |
| Application | Signal, Wire-to-Board |
| Comments | See Product Specification for maximum current rating by circuit size and wire AWG |
| Component Type | PCB Receptacle |
| Product Name | CLIK-Mate |
| UPC | 822350916936 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 3.0A |

Downloaded from Arrow.com.

| | |
|---|---|
| Voltage - Maximum | 250V AC (RMS)/DC |

### Physical

| | |
|---|---|
| Circuits (Loaded) | 9 |
| Circuits (maximum) | 9 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Mated Height | 10.90mm |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 1031.000/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | Yes |
| Pitch - Mating Interface | 2.00mm |
| Plating min - Termination | 1.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Surface Mount |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| 2.00mm Pitch CLIK-Mate Single Row Plug Housings | 502439 |

Downloaded from Arrow.com.

Downloaded from Arrow.com.