Datasheet for part number TR1619RFH1NB

Our Catalog Part Number: TR1619RFH1NB
Our Global Manufacturing Part Number: 192990-1690
Brand: Cannon Product Category: Trident Product Line: Trident Series: TR

Product Datasheet	
Series	Trident Ringlock
Connector Type	Receptacle for Flange Mounting
Environmental Sealing	IP65
Sealing Methode	with Interface Seal
Shell Size	16
Contact Quantity	19
Contact Gender	Socket
Contacts included	No, order separately
Operating Voltage	48 Vac, 60 Vdc
Current Rating	Up to 13 A
Operating Temperature	-55°C to +105°C
Insulator Resistance	5000 Megaohms at 500 V dc
Durability	Up to 500 Mating Cycles
Flammability	UL94-V0
Salt Spray	48 hours
Vibration	10 g's peak, 10 to 500 Hz, 9 hours
Physical Shock	50 g's peak, 11msec., half-sine pulse
Insulator Material	Black Nylon
Coupling Nut Material	Nickel Plated Zinc Alloy
Sealing Grommet Material	Silicone Rubber
Mounting Style	Interface Sealing

Specifications and dimensions subject to change.

Downloaded from Arrow.com.