







1. CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION.
2. CONNECTOR IS SUPPLIED WITH CONTACTS AS LISTED IN TABLE.
3. KEYING SHOWN IN POSITION "01" FOR ILLUSTRATION ONLY. CONNECTORS SHIPPED WITH KEYING INSTALLED IN POSITION PER TABLE. FOR POSITION "00" KEYING HARDWARE SHIPPED UNASSEMBLED.


COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	ELECTROLESS NICKEL PER MIL-C-26074
INSERT RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	ELECTROLESS NICKEL PER MIL-C-26074
FLAT HEAD SCREWS	STAINLESS STEEL	PASSIVATED
POLARIZING KEYS	ZINC ALLOY PER ASTM-B-86	-
INSERTS	THERMOSET OR THERMOPLASTIC PPS PER MIL-M-24519	-
POLARIZING KEY RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625
-	-	-

47	MODULE A 211431-4 (SIZE 22 POSTED; QTY=150) MODULE B 211431-4 (SIZE 22 POSTED; QTY=150) MODULE C 211431-4 (SIZE 22 POSTED; QTY=80) 2-448138-6 (SIZE 20 POSTED; QTY=4) 2-448139-5 (SIZE 16 POSTED; QTY=1)	1883329-3
01	MODULE A NONE MODULE B NONE MODULE C NONE	1883329-2
01	MODULE A 211431-4 (SIZE 22 POSTED; QTY=150) MODULE B 211431-4 (SIZE 22 POSTED; QTY=150) MODULE C 211431-4 (SIZE 22 POSTED; QTY=80) 2-448138-6 (SIZE 20 POSTED; QTY=4) 2-448139-5 (SIZE 16 POSTED; QTY=1)	1883329-1
KEYING POSITION	CONTACTS INCLUDED AND INSTALLED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 4-24-06	TE Connectivity	
		CHK K.HOGAN 4-24-06		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD K.HOGAN 4-24-06	NAME	RCPT ASSY, SIZE 2, ARINC 600 (150/150/85)
	0. PLC ± -	PRODUCT SPEC	SIZE	CAGE CODE
	1. PLC ± -	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	A1 00779	1883329
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 2	REV E

LOC		DIST		REVISONS			
P	L	T	R	DESCRIPTION	DATE	DWN	APVD
-	-	-	-	SEE SHEET #1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 4-24-06	 TE Connectivity				
		CHK K.HOGAN 4-24-06					
DIMENSIONS: INCHES		APVD K.HOGAN 4-24-06	NAME RCPT ASSY, SIZE 2, ARINC 600 (150/150/85) —	SIZE A1	CAGE CODE 00779	DRAWING NO C1883329	RESTRICTED TO —
		PRODUCT SPEC APPLICATION SPEC —					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		FINISH —	WEIGHT —				
MATERIAL SEE TABLE		SEE TABLE		CUSTOMER DRAWING			
				SCALE 1:1	SHEET 2 OF 2	REV E	