




22 mm IP68 FIELD TERMINATION KIT

SPECIFICATIONS

For complete specifications and processing guidelines see www.samtec.com?ACPK-22

Terminal Material:
Brass

Contact Material:
Brass/BeCu

Operating Temp Range:
-10 °C to +105 °C


Housing:
-P: Thermoplastic
-M: Zinc Alloy

RoHS Compliant:
Yes

Mates with:
ACR-22, ACRK-22

CURRENT RATING		
LEAD STYLE	PINS POWERED	CCC per PIN
-01	30	2.0 A
-02	20	2.3 A
-03	8	8.3 A

For general reference only. See www.samtec.com?ACPK-22 for complete test data or contact AccliMate@samtec.com for applications requiring higher current carrying capacity.



DUST CAP

- DCA-ACP-22-M-X (Metal)
- DCA-ACP-22-P-X (Plastic)



- Visit sealedio.samtec.com for a complete list of sealed systems

NOTE

For complete specifications and processing guidelines see www.samtec.com?ACPK-22

Note:
Some lengths, styles and options are non-standard, non-returnable.

ACPK

22

LEAD STYLE

PLATING

GENDER

HOUSING MATERIAL

KEYING OPTIONS

-01

= 1.0 mm DIA (30)
(20-24 AWG)

-02

= 1.0 mm DIA (20)
(20-24 AWG)

-03

= 1.5 mm DIA (8)
(14-18 AWG)

-G

= 10 μ" (0.25 μm)
Gold over
50 μ" (1.27 μm)
Ni on contact

-T

= Terminal

-S

= Socket

-P

= Plastic

-M

= Metal

-1

= Orange, 45°

