
737440-1 Product Details



Active

View 3D PDF

FASTON Uninsulated Receptacles & Housings

FASTON RECEP 6,35 LIF

737440-1

TE Internal Number: 737440-1

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Product Highlights View All

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Board Mount = No
- Receptacle Style = Straight

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Terminal
Receptacle Style	Straight
Insulation Support	Insulation Support
Wire/Cable Type	Stranded
Insertion Force	Low
Finish	None

Mechanical Attachment

Board Mount	No

Termination Features

Crimp Type	F-Crimp

Dimensions

Mating Area Interface Dimensions (mm [in])	6.35 x 0.81 [.250 x .032]
Insulation Diameter (mm [in])	2.36-3.30 [.093-.130]

Body Features

Weld Tab	Without
Wire Range (mm [AWG])	1.00-2.50² [17-13]
Material	Brass

Contact Features

Terminal Type	Receptacle

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Listed
CSA Certified	Yes

Conditions for Usage

For Hermetic Header Tab	No

Packaging Features

Packaging Method	Strip

Other

Line	Premier
Brand	AMP

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.