Part Number : 936040071
Product Description : Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 252 x 215 x 91mm Outside Dimensions, Grey RAL 7037
Series Number : 93604
Status : Active
Product Category : Die-cast Enclosures
Engineering Part Number : 8000.6295.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Die-cast Enclosures
Series	93604
Description	Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 252 x 215 x 91mm Outside Dimensions, Grey RAL 7037
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2
Type	ATEX
UPC	887191871462

Physical

Enclosure Coating	Polyester Powder
Enclosure Color	Grey RAL 7037
Internal Dimensions	239 x 202 x 85mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	External Flanges
Outside Dimensions	252 x 215 x 91mm
Packaging Type	Carton
Temperature Range - Operating	-20° to +85°C

Mates With / Use With

Use with Part(s)

Downloaded from Arrow.com.

Description	Part Number
Use With	DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

Downloaded from Arrow.com.