Industrial Power Strip, 9-Outlet, 15 ft. (4.6 m) Cord - Accommodates 1 Transformer

MODEL NUMBER: **UL17CB-15**







Highlights

- 9 outlets
- 15-ft. (4.57 m) cord
- 12.5" length
- All metal housing
- 9th outlet on end panel

Package Includes

- UL17CB-15 Power Strip
- Warranty information
- Instruction manual

Description

This PowerIt!™ UL17CB-15 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes nine NEMA 5-15R output receptacles, eight of them with 1.125-inch center-to-center spacing and a ninth outlet placed away from the rest on the panel opposite the input line cord to accommodate large plugs with minimal blockage. Includes 15-foot (4.6 meters) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL17CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 9 NEMA 5-15R output receptacles, 1-8 with 1.125 inch center-to-center spacing and a 9th outlet placed away from the rest on the panel opposite the input line cord to accommodate large plugs with minimal blockage
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332103512
Product Type	Power Strip
Charging Form Factor	Strip

Downloaded from Arrow.com.

Device Compatibility	Chromebook; Computer; Laptop; Monitor/HDTV; Phone; Projector; Tablet; Video Game System
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14 AWG
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(9) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of 8 plus 1 end-mounted outlet
Right-Angle Outlets	No
Outlet Spacing	1-8 spaced 1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	1.07 in.

Downloaded from Arrow.com.

Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.00 x 2.40 x 6.00
Shipping Dimensions (hwd / cm)	35.56 x 6.10 x 15.24
Shipping Weight (lbs.)	3.05
Shipping Weight (kg)	1.38
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Outlet Spacing	1-8 spaced 1.625 in.
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.