



Part Number : [1200698693](#)

Product Description : Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length

Series Number : 120069

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 884S31BS1M100



Documents and Resources

Drawings

[1200698693_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|-------------------------------------------------|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Reviewed per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

| | |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120069 |
| Description | Micro-Change (M12) Double-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Male (Straight) to Female (90°), 22 AWG, Black TPU WSOR Cable, 10.0m (32.81') Length |
| IP Rating | IP67 |
| Product Name | Micro-Change (M12) |
| Type | Double Ended |
| UPC | 889056132145 |

Agency

| | |
|----|---------|
| UL | E152210 |
|----|---------|

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 60V |

Physical

| | |
|----------------------|--------------------|
| Cable Diameter | 5.70mm (.224") |
| Cable Length | 10.0m (32.81') |
| Color - Cable Jacket | Black |
| Connector End A | Micro-Change (M12) |
| Connector End B | Micro-Change (M12) |

| | |
|-------------------------------|--------------------------|
| Coupling Style | Knurled Hexnut, Threaded |
| Gender | Female-Male |
| Keyway | A-Coded |
| LED Indicator | None |
| Material - Cable Jacket | TPU |
| Material - Connector Body | TPU |
| Material - Contact | Brass |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 1044.000/g |
| Orientation | 90° to Straight |
| Poles | 4 |
| Temperature Range - Operating | -25° to +85°C |
| Wire/Cable Type | UL 21215 |
| Wire Size (AWG) | 22 |

This document was generated on Jan 04, 2026