
# FGS-MEXP-LP-A/B/F



FiberGuide® 2-Inch Low profile Express Exit™, 4x4in, 4x6in, 4x12in, 4x24in, Yellow

## Product Classification

| | |
|---|---|
| **Regional Availability** | Asia \| Australia/New Zealand \| EMEA \| Latin America \| North America |
| **Portfolio** | CommScope® |
| **Product Type** | Express exit |
| **Product Brand** | FiberGuide® |
| **Product Series** | FGS |

## General Specifications

| | |
|---|---|
| **Color** | Yellow |
| **Orientation** | Horizontal |
| **Section Type** | Express exit |

## Dimensions

| | |
|---|---|
| **Height** | 132 mm \| 5.197 in |
| **Width** | 260 mm \| 10.236 in |
| **System Dimensions** | 102 mm x 102 mm (4 in x 4 in) \| 102 mm x 152 mm (4 in x 6 in) \| 102 mm x 305 mm (4 in x 12 in) \| 102 mm x 610 mm (4 in x 24 in) |

## Ordering Tree



©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

COMMSCOPE®

Downloaded from Arrow.com.

# FGS-MEXP-LP-A/B/F

| | 9 | | 10 |
|---|---|---|---|
| FGS | B | - MEXP - | A/B/F |

**Section Color**

| | | |
|---|---|---|
| 9 | empty | yellow |
| | B | black |

**Section Size**

| | | |
|---|---|---|
| 10 | A/B/F | 4 x 4/6/12 in, with 2 x 2 in exit |
| | E-A/B/F | 4 x 4/6/12 in, with 4 x 4 in exit |
| | F-F/H-NC | 4 x 12/18/24 in, with 4 x 12 in exit, no cover |
| | G-A/B/F | 4 x 4/6/12 in, with 4 x 6 in exit |
| | LP-A/B/F | 4 x 4/6/12 in, with 2 x 2 in exit, low profile |
| | LP-CA | 4 x 4/6/12 in, with 2 x 4 in exit, low profile |
| | LP-G | 2 x 6 in, with 2 x 2 in exit, low profile |
| | GS-ABF-NC | 4 x 4/6/12 in, with 4 x 6 in exit, no cover |
| | CV | cover |
| | NC | no cover |

## Material Specifications

**Material Type** Engineering Thermoplastic

## Environmental Specifications

**Flammability Rating** CSA S143 | UL 2024 | UL 94 V-0

**Halogen Characteristics** Blue Angel | TCO '99 | WEEE

**Safety Standard** CSA | UL

## Packaging and Weights

**Weight, net** 0.98 kg | 2.161 lb

## Regulatory Compliance/Certifications

| Agency | Classification |
|---|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

COMMSCOPE®

Downloaded from Arrow.com.