

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2025/03/02	Henry	New Initial.
B	C250633	2025/05/14	Henry	B X1
C	C250706	2025/05/28	Henry	C X4




Optional Accessory
可選配件

Through-Hole




Recommended Panel Cut-Out
建議開孔尺寸

Threaded-Hole



Recommended Panel Cut-Out
建議開孔尺寸



Recommended installation orientation
建議安裝朝向

Note:
* QC Important Dimension.
* Waterproof Rate: IP68(2m/1h)
* Body: Nylon+GF, Black.
* Membrane: ePTFE.
* B C O-Ring: Rubber, Red.
* C Air Permeability: 6~12L/min @ 7 kPa
* Temperature Resistance: -40~125℃
* Recommended plate thickness: T > 3.5mm.
* Recommended installing torque: 1.8~2.2N.m
* All Parts Are RoHS Compliant.

UNIT: mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE: BREATHABLE VENT, PLASTIC, M24

SCALE 1:1 | SIZE A4 | SHEET 1 OF 1
REV. C | WC-REV. .0 | QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
VT-BPM24BK-NO8001	Henry	2025-05-28
DWG NO: VT-BPM24BK-NO8001	CHECKED BY: Jerry	DATE: 2025-05-28
CUSTOMER: ALTW	APPROVED BY: Fred	DATE: 2025-05-28

WI0814-03-RW01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Downloaded from Arrow.com.