



+ CONNECTORS

TERMINAL BLOCK HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)
8P, SPRING FEMALE C,5.08MM, LSF
Buchanan

1986830-8
TE Internal Number: 1986830-8

- EU RoHS Compliant
- EU ELV Compliant
- Connector Style Receptacle
- Centerline (Pitch) 5.08 mm [.2 in]
- Number of Rows 1
- Wire Entry Angle Side
- Number of Positions 8

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

SPRING FEMALE CONNECTOR WITH LOCKING SCREW FLANGES PITCH 5.08mm

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Receptacle
Terminates To Printed Circuit Board
Block Type None
Shrouded No

Configuration Features

Number of Rows 1
Wire Entry Angle Side
Number of Positions 8
Side Stackable No
Closed End Without

Electrical Characteristics

Current Rating (Max) (A) 12
Voltage (VAC) 300

Body Features

Interlock Without

Contact Features

Contact Base Material Copper Alloy
Contact Mating Area Plating Material Tin

Mechanical Attachment

Screwless Terminal Block Yes
Screw Flange With

Housing Features

Centerline (Pitch) 5.08 mm [.2 in]
Housing Material PA 6.6
Housing Color Green

Dimensions

Wire Range .05 – 3 mm² [30 – 12 AWG]

Packaging Features

Packaging Quantity 100
Packaging Method Box

Statement of Compliance

Statement of Compliance
PDF