

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10127717-16LF* > 10127717-16LF

10127717-16LF

10127717-16LF - Minitek® Pwr 3.0 : Minitek® Pwr 3.0 Plug Housing, Dual row, 16 positions Glow Wire Compatible



Customer drawing

Product Environmental Compliance Report

ACTIVE

RoHS Compliant

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features	
General	
Number of contacts	16
Series	10127717
Dimensional	
Pitch	3.0
Electrical	
Withstanding Voltage	1000 VAC
Current rating	Up to 5 Amps
Resistance (Contact)	20 milliohm max. final 10 milliohm max. initial
Resistance (Insulation)	1000MΩ min
Voltage rating	250V
Mechanical	
Durability (Mating cycles)	100 Cycles
Insertion force	4.5N max
Withdrawal Force	2N min before durability, 1.5N min after durability
Glow Wire Compatible	Yes
Physical	
Color (Housing)	Black
Material (Housing)	High Temperature Thermoplastic
Temperature (Range)	-40°C to +105°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	ML E467317
Other Features	
Packaging (Type)	PE Bag

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.