

Home: >

Part Number: 130057-0005
ENET MALE ATTACHABLE PG9 UV

Image not available

Status: Active
Series: [130057](#)
Category: Molex Parts
Old Part Number: ENSAM315-V

 [CHECK DISTRIBUTOR INVENTORY](#)

 [Add to My Parts](#)

Go to [Part Detail](#) ▼

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant

China RoHS: 

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed



Product Compliance Statement

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

▼ **General**

Status	Active
Category	Molex Parts
Series	130057
UPC	78678850481

▼ **Physical**

Net Weight	5.260/g
------------	---------

▼ **Material Info**

Old Part Number	ENSAM315-V
-----------------	------------

Molex Connectors

Wire-to-Board
Board-to-Board
Wire-to-Wire
Input/Output (IO)
FFC/FPC
Sockets

Other Products

Fiber Optic Products
Antennas
Industrial Automation
Membrane Switches
Copper Flex
PCB Assemblies
Woodhead Electrical
Solid State Lighting

Resources

Contact Us
Catalog
Cross-Reference
Industries
Literature
Product Name

Company Info

About Us
Careers
ecocare
Investors
Press Room
Shows & Events
Supplier Portal

Other Info

Feedback
Help
Legal Disclaimer
View Mobile Site
Privacy Policy
Sitemap

Stay Connected with Molex:

