



Part Number : [15975041](#)
Product Description : Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 4 Circuits, Black
Series Number : 30067
Status : Active
Product Category : Connector Housings
Engineering Number : 30067-04A2



Documents & Resources

Drawings
[015975041_sd.pdf](#)

Specifications
[PK-30067-001-001.pdf](#)
[PS-45750-001-001.pdf](#)
[PS-5556-003-001.pdf](#)
[TS-30067-001-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Connector Housings |
| Series | 30067 |
| Description | Mini-Fit TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 4 Circuits, Black |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Comments | Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current derating information. Connector Position Assurance |
| Product Name | Mini-Fit TPA |
| UPC | 800753595897 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Physical

| | |
|--------------------|------------|
| Breakaway | No |
| Circuits (maximum) | 4 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | No |

| | |
|-------------------------------|----------------|
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Polyester |
| Net Weight | 1.671/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 4.20mm |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---|--------------|
| Mini-Fit TPA Dual Row Vertical Headers | <u>30069</u> |
| Mini-Fit TPA Dual Row Right-Angle Headers | <u>30070</u> |

Use with Part(s)

| Description | Part Number |
|---|--------------|
| Mini-Fit TPA Keys | <u>30072</u> |
| Mini-Fit Connector Position Assurance Key | <u>30071</u> |
| Mini-Fit Female Crimp Terminals | <u>5556</u> |
| Mini-Fit Plus Female Crimp Terminals | <u>45750</u> |

This document was generated on Feb 07, 2025