



Protect your electronics investment without breaking your budget. This surge suppressor guards against damaging spikes and surges, providing a secure barrier for your sensitive electrical equipment and precious data. The negative effects of Electromagnetic and Radio Frequency Interference (EMI/RFI) are also kept in check by a built-in noise filter.

Wall-mountable, impact-resistant ABS plastics keep the unit looking good for years to come. 14 AWG suppressor power cord is 4 feet long. For indoor use only. Plus, three outlet saver extension cords are included to keep your surge suppressor and UPS outlets from being blocked by bulky AC transformers!

Suppressor Input: Six NEMA 5-15 Female

Features & Benefits

Guards against damaging spikes and surges

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120355496	Country Of Origin	China
Number of Receptacles	6	Application Sector	Commercial, Residential
Type	Power Strip, Surge Suppressor		

Technical Information

Wire Gauge	18 AWG	Amperage	15 A
Voltage	6500.0 V		