



SN14, Nylon Splice For 16 - 14 AWG

By Burndy
Catalog # SN14



Copper Butt Splice, 16-14 AWG, 1.25" Splice Length, Nylon Insulated, Tin Plated, 600 Volts Max.

Features

- Seamless tubing, high quality design without seams to split
- Electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properies
- Tin plating provides durable long-lasting resistance to corrosion
- Positive center wire stop for proper depth of wire insertion
- Nylon is locked into position

Application

For Heavy Duty Application Requirements

General

| | |
|--------------------|----------------------|
| Catalog Number | SN14 |
| Color Code | Blue |
| Connector Type | Seamless Butt Splice |
| EU RoHS Indicator | Yes |
| Insulation | Y |
| Insulation Type | Nylon |
| Material | Copper |
| Plated | Y |
| Plating Type | Unplated |
| Sub Brand | INSULINK |
| Temperature Rating | 105 |
| Trade Name | INSULINK™ |
| Type | SN |
| UPC | 781810736982 |
| UPC 14 Digit GTIN | 00781810736982 |

Dimensions

| | |
|------------------------------------|---------|
| Cable Insulation Diameter Maximum | 0.15 in |
| Dimension - Diameter Max Size inch | 0.15 in |
| Dimension - L Length Overall mm | 32 mm |
| Dimension - Length Overall inch | 1.25 in |

| | |
|-----------------------------------|---------|
| Dimension - Outside Diameter inch | 0.15 in |
| Dimension - Strip Length inch | 3/16 in |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Conductor Related

| | |
|-----------------------------------|---------------|
| Conductor - Copper Str Size | 16 AWG;14 AWG |
| Conductor - Copper Str Size Range | 16 - 14 AWG |
| Conductor Size | 16 - 14 AWG |

Certifications And Compliance

| | |
|--------------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL486 |
| Standards - Industry Standards | UL486 |
| Met | |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 600 |
| Minimum Pack Quantity | 50 |
| Pallet Quantity | 99999 |

Product Assets

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_SN10_LineArt](#)
[Sales Drawings - 50094191](#)
[Specifications - SN14](#)

