Single Contact Candelabra Bayonet

11 SERIES

- **SINGLE CONTACT CANDELABRA BAYONET GROUNDED LAMPHOLDERS**
- **6" WIRE LEAD • ELECTRO-TINNED PLATED STEEL SHELL**
- **MAXIMUM RATING: 25 WATTS, 12 VOLTS**

Overview

The 11 Series lampholders are constructed with a electro-tinned plated steel shell with a brass center contact mounted on a phenolic insulating disc with one 6" wire lead. The brackets are grounded to the shell. Lampholders are designed for use in low voltage lamp applications with single contact candelabra bayonet lamps.

Specifications

Shell: *electro-tinned plated steel.*

Custom shells also available:

Single contact indexed shell: *add* ***-DX*** *to end of part number. For example,* ***11-207*** *changes to* ***11-207-DX*** *for indexed shell. Shell is only available in zinc plated steel.*

Brass Shell: *add* ***-BR*** *to the end of a part number. For example,* ***11-207*** *changes to* ***11-207-BR*** *for brass shell.*

Center contact: *nickel plated brass supplied with phenolic insulating disc.*

Custom contact also available.

Glass Melamine Center Contact: *for outdoor environments.*

Spring: *zinc plated steel. A custom stainless steel spring is also available.*


Wire leads: 6" lead: *#18 AWG, black, bare copper, PVC insulated, UL/CSA rated 105° C, stripped 1/2". Grounded units are supplied with one 6" wire lead. Custom wire lengths, stripping, termination and wire types are also available.*

Second ground wire: *White #18AWG, attached to the spring. Add* ***-2W*** *to end of part number to order.*


Mounting: Brackets: *0.025" to 0.032" zinc plated steel. Custom brackets and plating types are available.* ***Plug button*** *and* ***threaded bushing*** *(supplied hex nut and lockwasher) also available.*

Maximum rating: *25 Watts, 12 Volts.*

Grounded only. ***11-207***



Grounded only. ***11-230BN***



Suggested Mounting Hole 13/32" Diameter.

Can't find it here? We have many more standard and custom solutions

For further information, phone Customer Service at 800.522.5546.

Downloaded from Arrow.com.


Single Contact Candelabra Bayonet

11 SERIES

Electro-Tinned Plated Steel Shell
Grounded
6" Wire Lead


Maximum Rating: 25 Watts, 12 Volts

11-202




Grounded only.

11-208




Grounded only.

11-211




Grounded only.

11-212




Grounded only.

11-215
11-218
11-282



Grounded only.

Mounting Hole Diagram



Bracket No.	"A" Dimension
-15	1-5/32"
-18	1-13/32"
-82	15/16"
Maximum Panel Thickness .045"	

Downloaded from Arrow.com.


Single Contact Candelabra Bayonet

11 SERIES

Maximum Rating: 25 Watts, 12 Volts


Electro-Tinned Plated Steel Shell
Grounded
6" Wire Lead

11-223




Grounded only.

11-225




Grounded only.

11-226




Grounded only.

11-227



Grounded only.


11-240



Plug button: zinc plated steel, for 15/16" hole with panel thickness range 1/32" to 5/64".

Grounded only.

11-240X



Plug button: zinc plated steel, for 15/16" hole with panel thickness range 1/32" to 5/64".

Grounded only.

Downloaded from Arrow.com.


Single Contact Candelabra Bayonet

11 SERIES

Electro-Tinned Plated Steel Shell
Grounded
6" Wire Lead

Maximum Rating: 25 Watts, 12 Volts


11-240XT



Plug button: zinc plated steel, for 15/16" hole with panel thickness range 1/32" to 5/64".


Grounded only.

11-245




Grounded only.

11-255




Grounded only.

11-260



Grounded only.


11-272



For reversed bracket:
Grounded unit: ***11-271.***

Grounded only.

11-275



Grounded only.

Downloaded from Arrow.com.