Part Number : 349590347
Product Description : Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, without CPA, 34 Circuits, Polarization Option A, Black
Series Number : 34959
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

349590347_sd.pdf

PK-31301-538-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

349590001-AS-CH-000.pdf

AS-34959-001-001.pdf

PS-34959-001-001.pdf

TS-34961-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	34959
Description	Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, without CPA, 34 Circuits, Polarization Option A, Black
Application	Automotive, Wire-to-Board
Component Type	Receptacle
Product Name	Mini50
UPC	887191704470

Physical

Circuits (maximum)	34
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.700/g
Number of Rows	3
Packaging Type	Bag

Downloaded from Arrow.com.

Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	A
Polarized to Mating Part	Yes
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +105°C
Terminal Size	0.5, 0.635

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Vertical Hybrid Header, UL 94 HB, 3 Rows, 34 Circuits, Polarization Option A, Black, Tube	349587340
Mini50 Unsealed Vertical Hybrid Header, UL 94 HB, 3 Rows, 34 Circuits, Polarization Option A, Black, Tape and Reel	349588340
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tube	349617343
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tape and Reel	349618343
Mini50 Unsealed Right-Angle Hybrid Header, UL 94 HB, 34 Circuits, Polarization A, Black, Tray	349610343
Mini50 Unsealed Vertical Hybrid Header, UL 94 HB, 3 Rows, 34 Circuits, Polarization Option A, Black, Tray	349580340
Mini50 Unsealed Right-Angle	213355

Downloaded from Arrow.com.

Headers	

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	560023

Downloaded from Arrow.com.