



Datasheet for part number DEUE9PK87F0

Our Catalog Part Number: DEUE-9P-K87-F0
Our Global Manufacturing Part Number: 110972-0048
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*U

Product Datasheet	
General	Low Cost Crimp Connector
Wire Gauge Range AWG	AWG 18-30
Mating Cycles	50, 200, 500
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	5 A max
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin/nickel
Insulator Material	glass filled Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	9 contacts size 20
Gender	Pin
Contacts	delivery without contacts, please order separately
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold over nickel
Contact Termination	Crimp
Mounting Methode	4-40 Clinchnut

Specifications and dimensions subject to change.