




Part Number : [150140413](#)
Product Description : 0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 13 Circuits
Series Number : 15014
Status : Active
Product Category : Flat-Flexible Cable (FFC)




Documents & Resources

Drawings
[150140413_sd.pdf](#)

Specifications
[1501400001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15014
Description	0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 13 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	191130093281

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Physical

Cable Length	102.00mm
Circuits (Loaded)	13
Contact Layout Type	A (same side)
Design Feature	Miniaturization
Material - Plating Mating	Gold
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Mating Interface	0.25mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flexible Printed Circuitry
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

0.25mm Pitch Easy-On FPC Connector, 1.00mm Mated Height, Right-Angle, Surface Mount, Bottom Contact Style, with Extended Actuator, 13 Circuits, Halogen-Free, 6000 Pieces per Reel	<u>5020781362</u>
---	-------------------

This document was generated on Feb 03, 2025