



Johanson Product Information for 0868AT43A0020001E

Johanson Company: Johanson Technology inc. Product Release Date: 26 July, 2007

Deprecated P/N: 0868AT43A0020E

Datasheet Date: 07-21-2024

Description: Antennas, 2708, 858-878MHz, 3W, -1dBi (typ), For small form factor applications , Ni/Sn (RoHS), 7" Reel Embossed Tape

Life Cycle Stage: Active - Production

Schedule B: 8529

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Antennas

Product Subfamily: Antennas

Marking: Orientation Mark

Web Page Link:

<https://www.johansontechnology.com/antennas>

Thickness (Max): 0.035

Thickness (Min): 0.023

End Band (Min):

End Band (Max):

Standard Item: 1

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 20

Length (Min): 0.268

Length (Max): 0.284

Width (Min): 0.071

Width (Max): 0.087

Packaging: 7" Reel Embossed Tape

Packaging Qty: 1000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -55°C to +125°C

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%