

A

B

C



D

E

F

G

H



Material:

- Cable: UL 20276 #28 18 P+1(#26)+AL/MY+85%Braid O.D:7.5
- Connector:DB25M, Blue
DB25F, Blue
- Thumbscrew: #4-40UNC, E23
- Copper Tape: 30X95

Notes:

1. Total Length: See Item No.
2. Color: Beige
3. Molded Type
4. 360° Solder

Scale	1:1						Name	Item No. AK733-1.8 (1.8 Meters) AK734-3 (3.0 Meters) AK735-5 (5.0 Meters)	
TOLERANCE					Drawn	11.11.11	Chappell		
X.X	±0.40								
X.XX	±0.25				Approved				
X.XXX	±0.15							Title IEEE 1284 Bi-Directional Extension Cable, D-Sub 25 Pin Male to D-Sub 25 Pin Female	
Angle	±3°								
								Drawing No.	rev00

