

Search within category

GO

BUY NOW

DESIGN / INSTALL



PLT3S-M

Pan-Ty® locking tie, standard cross section, 11.5 (292mm) length, nylon 6.6, natural, bulk package.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Nylon 6.6				
Application	General				
Color	Natural				
Cross Section	Standard				
Locking Style	Locking				
Plenum-Rated	Yes, AH-2				
Tool	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STS2, STH2				
Length In (mm)	11.50 (292.0)				
Thickness In (mm)	0.05 (1.3)				
Bundle Diameter Range In. (mm)	0.06 (1.5) - 3.00 (76.0)				
CE Compliant	Yes				
CSA Certified	Yes				
Mil. Std. Part Number	MS3367-7-9				
UL 62275 Compliant (Type 1, 11)	No				
UL 62275 Compliant (Type 2S, 21S)	Yes				
UL Listed (File #E56854)	Yes				
UL Recognized (File #E56854)	Yes				
Continuous Use Temperature Range	-76°F (-60°C) - 185°F (85°C)				
Environment	Plenum				
Installation Temperature	-4°F (-20°C) - 32°F (0°C)				
Min. Loop Tensile Strength (Lbs.)	50.00				
Min. Loop Tensile Strength (N)	222				
Operating Temperature	-76°F (-60°C) - 185°F (85°C)				
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.				
Width In (mm)	0.19 (4.8)				
RoHS Compliance Status	Compliant				
Min. Order Qty.	1,000				