

Part Number : [936000063](#)

Product Description : Heavy-Duty Metal Gable Gland - 5 Bar, for 4.00-10.00mm Cable, M16x1.5 Thread

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands

Engineering Part Number : 7000.6896.0




Documents and Resources

Drawings

[936000063_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Gable Gland - 5 Bar, for 4.00-10.00mm Cable, M16x1.5 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191829852

Physical

Cable Diameter	4.00-10.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	25.000/g
Packaging Type	Bag
Panel Cutout Diameter	16.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	M16x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Industrial connector hoods and housings

This document was generated on Apr 21, 2026