



Part Number : [731740910](#)
Product Description : DIN 1.0/2.3 Plug, Straight, Crimp, Belden 1855A Cable, Push-pull Coupling, Brass Body, Nickel (Ni) Plated, Tray, 75 Ohms
Series Number : 73174
Status : Active
Product Category : RF / Coaxial Connectors

Documents & Resources

Drawings

[731740910 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73174
Description	DIN 1.0/2.3 Plug, Straight, Crimp, Belden 1855A Cable, Push-pull Coupling, Brass Body, Nickel (Ni) Plated, Tray, 75 Ohms
Application	RF
Product Name	DIN 1.0/2.3
Style	Cable
Type	Subminiature
UPC	884982298149

Electrical

Frequency	3 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 250 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	4.243/g
Orientation	Straight
Packaging Type	Tray

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	Belden 1855A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 24, 2025