



Part Number : [1301540058](#)
Product Description : Watertite Extreme Standard
Molded W Cordset, 2 Pole/3 Wire, Cordset Length
0.91m (3.0'), NEMA L5-15, 125V
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Number : 24W47-W

Documents & Resources

Drawings
[1301540058 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	Not saleable
EU ELV	Not saleable
Low-Halogen Status	Not saleable
REACH SVHC	Not saleable
EU RoHS	Not saleable

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Watertite Extreme Standard Molded W Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA L5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Molded W Cordset
UPC	78678800636

Agency

CSA	LL52750
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No

Locking Blade	Yes
Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Triple

This document was generated on Sep 22, 2025