# Johanson Part Number Information

11-13-2022

| | |
|---|---|
| Johanson Part Number: | LRC0402CJ33NGV001T |
| Legacy P/N: | L-07C33NJV6T |
| Description: Ceramic Inductor, 0402, 33nH±5%, 200mA, Ni/Sn (RoHS), Orientation Mark Full Marking, 7" Reel Paper Tape | |
| Life Cycle Stage: | Active - Production |
| AEC Q200 Qualified: | No |
| Schedule B: | 8504.50.0000 |
| Harmonization Code: | 8504.50.40.00 |
| ITAR: | No |
| ECCN: | EAR99 |
| RoHS Compliance: | Yes, RoHS 10/10 |
| REACH: | Yes |
| Country of Origin: | TW |
| Product Family: | Inductors |
| Product Subfamily: | Ceramic Inductors |
| Tolerance: | ±5% |
| Termination: | Ni/Sn (RoHS) |
| Marking: | Orientation Mark Full Marking |
| Product Release Date: | 03 January, 2006 |
| Web Page Link: | |

| | |
|---|---|
| Johanson Company: | **Johanson Technology Inc.** |
| NCNR: | No |
| Thickness (Max): | 0.024 |
| Thickness (Min): | 0.016 |
| End Band (Max): | 0.013 |
| Standard Item: | No |
| Lead Time Typical (Weeks)*: *This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. | 14 |
| Length (Min): | 0.035 |
| Length (Max): | 0.043 |
| Width (Min): | 0.016 |
| Width (Max): | 0.024 |
| Part Weight (mg): | 0.980 |
| Packaged Weight (lb) Arm: | 0.300 |
| Packaging: | 7" Reel Paper Tape |
| Packaging Qty: | 10000 |
| Operating Temp Range: | -40°C to + 100°C |
| Storage Temp Range (Packaged): | -10°C to +40°C |
| Storage Temp Range (Non Operating): | -40°C to +125°C |
| Download this information page | |



© All rights reserved. Johanson Technology

Downloaded from Arrow.com.