



Pushing Performance
Since 1945

Han 3A RJ45 10G Cat6 plug insert, 8p IDC




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 100 1560
Specification	Han 3A RJ45 10G Cat6 plug insert, 8p IDC
HARTING eCatalogue	https://b2b.harting.com/09451001560

Identification

Category	Connectors
Series	RJ45
Element	Cable connector
Specification	RJ45

Version

Termination method	IDC termination
Size	Han [®] 3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	Connector insert

Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm ² Stranded
	0.22 ... 0.32 mm ² Solid
Conductor cross-section	AWG 27/7 ... AWG 22/7 Stranded
	AWG 27/1 ... AWG 22/1 Solid
Wire outer diameter	1.6 mm
Transmission characteristics	Cat. 6 Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +70 °C
Cable diameter	6.5 ... 9.5 mm

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	35 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140058699
eCl@ss	27440205 Contact insert for industrial connectors