

Home > Avionics > MIL-STD-1553 > Transceivers > HI-25850 > HI-25850PBTF

HI-25850PBTF

[Overview](#)

[Quality & Reliability Info](#)



Package Description:	121 Low Profile Ball Grid Array (BGA)
Temp Range:	-55°C to +125°C
Flow:	T
RoHS Compliant:	Yes
Theta JA (°C/W):	22.5
Theta JB (°C/W):	12.1
Moisture Sensitivity Level:	3
Product Longevity:	> 10 years
Pricing:	Call for pricing

[REQUEST A QUOTE](#)

[REQUEST SAMPLES](#)