

Duplex Multimode 62.5/125 Fiber Patch Cable (MTRJ/ST), 3M (10 ft.)

MODEL NUMBER: N308-010



Description

Tripp Lite's 10-ft. (3.05 m) multimode duplex fiber optic MTRJ/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has MTRJ to ST connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-ft. (3.05 m) Connectors: MTRJ to 2 ST
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10-ft. (3.05 m) or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
UPC Code	037332042040
Technology	Multimode

Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Loop-back cables provide an easier, "single-person" solution for testing fiber optic cable systems

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with MT-RJ/ST connectors

Package Includes

- 10-ft. (3.05 m) Duplex MMF Cable MTRJ/ST 62.5/125 Fiber



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.triplite.com

Optical Mode	OM1
PHYSICAL	
Cable Jacket Color	Orange
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Shipping Dimensions (hwd / cm)	0.64 x 15.24 x 16.51
Shipping Dimensions (hwd / in.)	0.25 x 6.00 x 6.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	MTRJ DUPLEX (MALE)
Side A - Connector 2	ST DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.triplite.com/products/product-certification-agencies>