










Load vacuum cover




(All contacts and grounds)



PCB layout, component side



Z (5:1)



Max. Temperature: 260°C during 10 seconds
Find further technical information on DS 09550200302

0955 169 6822 333	2	4-40 UNC	Black insulator	Samples
0955 169 3821 741	1	M3	Black insulator	Reel packing: 140 connectors
0955 169 3822 741	1	4-40 UNC		
0955 169 6821 741	2	M3		
0955 169 6822 741	2	4-40 UNC		
0955 169 7821 741	3	M3		
0955 169 7822 741	3	4-40 UNC		
Part number		PL	Nut	Index designation

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN		Date 2018-11-29		State Final Release			
Department EL PD		Title D-Sub str SMT 9-pole male withh screwlock & ground pin								Doc-Key / ECM-Nr. 100236621/UGD/001/C 500000139800					
HARTING Electronics GmbH		Type TB		Number 0955169X82X								Rev. C		Pag 1/	
D-32339 Espelkamp															