

Save 20% On Your Next Order!

Thank you for your business.

Reveal Your Code >

Browse All Products

| Cat5e / Cat6 / Cat6a

| Cat6

| Cat6 Snagless Patch Cables

Loading...

Press image to zoom

15FT CAT6 SNAGLESS
UNSHIELDED (UTP) ETHERNET
NETWORK PATCH CABLE -
BLACK

Snagless design for network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications.

5,129 In Stock & ready to ship!

1

Add

PayPal

VISA

AMERICAN EXPRESS

DISCOVER

print

share

chat

Product # : 22014

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Product Description

Product Features

Product Specifications

Product Uses

Product Support

Product Description

For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Product Features

- Snagless design protects clips when plugging and unplugging
- Standard RJ45 connectors and unshielded twisted pair wires
- Available in 10 colors to color-code a network
- Available in lengths up to 150ft

Tap an icon to learn more:

Downloaded from Arrow.com

Product Specifications

Color :	Black
Length :	15.00 Foot
Jacket Rating :	Standard Non-Rated
UPC :	757120220145
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.442 LB

Electrical Characteristics

- Conductor DC Resistance - 9.38Ω/100m (maximum)
- Impedance - 100Ω
- Capacitance - 5600pf/100m
- Propagation Delay - 545ns/100m (maximum)
- Delay Skew - 45ns/100m (maximum)

Physical Characteristics

- Wiring Scheme - T568B
- Standard: Category 6 TIA/EIA-568-B-2.1, draft 9
- Connector: 50 micron gold-plated RJ45
- Temperature Rating - 60°C
- Voltage Rating - 30V
- Approvals - RoHS Compliant
- Warranty - Lifetime
- Package Type - Polybag

Conductor (Qty. 4 twisted pair)

- Conductor Type - 24AWG (7/0.20), Stranded Bare Copper
- Insulation - H-D PE
- Diameter - 0.98 ± 0.05mm
- Colors - Blue, Blue-White, Orange, Orange-White, Green, Green-White, Brown, Brown-White

Connector Type (Qty. 2)

- Connector Type - 8P8C (RJ45)
- Gender - Male
- Connector Material - Polycarbonate
- Contact Material - Copper Alloy, Gold Plating - 50µm
- Hood Material - Molded PVC

Overall Cable

- Jacket - PVC
- Minimum Average Thickness - 0.60mm
- Outer Diameter - 6.20 ± 0.30mm

Product Uses

- Gigabit 1000 BASE-T; 100 BASE-T; 10 BASE-T (IEEE 802.3)
- 4/16 Mbps Token Ring (IEEE 802.5); 100 VG-AnyLAN
- 100 Mbps TP-PMD (ANSI X3T9.5); 55/155 Mbps ATM
- Voice; T1

Product Support

Downloads

- Download the [technical specifications](#)

Recently Viewed...



Recently Viewed...

Info

About Us
Order History
Where To Buy
More ▾

Service

Contact Us
OEM Solutions
Tech Support
More ▾

Resources

Connector Guides
ConnectXpress
Drivers & Manuals
More ▾

Have A Question?

Get help with [Chat](#)
Call C2G **800.506.9607**



United States | Europe +

Copyright © 2018 C2G. All Rights Reserved

