



Part Number : 1301430192
Product Description : Watertite Cordset 14 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L5-15, 125V, Inline GFCI
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Number : 24W47B143IN



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices

Series	130143
Description	Watertite Cordset 14 Gauge SJOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L5-15, 125V, Inline GFCI
IP Rating	IP67
NEMA Configuration	NEMA L5-15
Product Name	Watertite
Specialty	N/A
Type	Cordset
UPC	78678871203

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SJOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	265.000/kg
Poles	2-pole/3-wire
Receptacle Type	Single