



Connector Location A

Connector Location B




X female



Loading-Plan

	Shield
1	White
2	Brown
3	Green
4	Yellow
5	Grey
6	Pink
7	Blue
8	Red



4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

8x0.25mm², PVC, grey	21347500820XXX
Type of cable	Part no.

- Protection level: IP67
- Temperature range: -25°C ... +80°C

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by COSTEA Costea		Inspected by STOCHECIC Stoccheci		Standardisation MUNTEANV Muntean		Date 2019-01-14	
Department HCS - RO		Title M12 Cable Assembly A-cod st/- f/-		State Final Release		Doc-Key / ECM-Nr. 100805933/UGD/000/A 500000144866		Rev. A	
HARTING Customised Solutions		Type TB		Number 21347500820XXX		Page 1/1			
D-32339 Espelkamp									