


TABLE 1		
DASH NO	DESCRIPTION	
-1	TERM (NO CHAIN)	
-2	TERM WITH 2.5 BRASS CHAIN	
-3	TERM WITH 2.5 NYLON CHAIN	
-4	TERM WITH 3.0 BRASS CHAIN	
-5	TERM WITH 3.0 NYLON CHAIN	
-6	TERM WITH 6.0 BRASS CHAIN	
-7	TERM WITH 6.0 NYLON CHAIN	
-8	TERM WITH 4.0 BRASS CHAIN	
-9	TERM WITH 4.0 NYLON CHAIN	





NOTE LENGTH FOR SST ROPE WITH MTG LUG OPTION IS NOT MEASURED TO CENTER OF BULKHEAD MTG LUG




5. EXAMPLE OF COMPLETE MODEL NO:
TNA1 - 2 - 3 - D2
BASIC MODEL NO
TNH1 (50 OHM)
UTNH1 (75 OHM)
CHAIN/ROPE MATL AND LENGTH (SEE TABLE 1)
BULKHEAD JACK MOUNTING LUG (OPTIONAL) AVAILABLE WITH BRASS CHAIN, NYLON CHAIN & SST ROPE (SEE TABLE 2)

4. TERMINATED MALE COAXIAL 50 & 75 OHMS TNC TYPE PLUG WITH CHAIN & MOUNTING LUG OPTIONS
3. RESISTANCE VALUE IN OHMS (1/2W, 1%)
S = PIN SHORTED TO CASE (NO RESISTOR)
2. FINISH: TFS-1A (NICKEL)
1. ALL DIMENSIONS ARE IN INCHES

TABLE 2				
DASH NO	"A" DIA	"B" DIA	"C" DIM	"D" DIA
-D2	.630	.750	1.066	.450
-D3	.505	.625	.941	.388
-D4	.439	.562	.878	.355
-D5	.380	.500	.816	.325
-D6	.317	.437	.753	.295
-D7	.281	.406	.722	.278
-D8	.610	.750	1.066	.450
-D9	.567	.687	1.003	.419
-D10	.192	.312	.628	.231
-D11	1.005	1.125	1.441	.638
-DD8	.330	.450	.766	.300



RED INDICATES ORIGINAL



REVISIONS		102-0006	SH 1
REV	DESCRIPTION	DATE	APPROVED
AC	REVISED PER ECD 15106	7/1/03	W3

INTERPRET DRAWING PER MIL-STD-100 DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED		TOL: UNLESS SPECIFIED .XX ± .02 .XXX ± .010 .XXXX ANGLES		TROMPETER RF connectivity a cinch connectivity solutions brand	
DRAWN JCM	DATE 6-30-03	CHECKED	DATE 6-30-03		
QUALITY	DATE 7/1/03	HANDS	DATE 7/1/03	FINISH:	TITLE: TNA1/LTNA1
APPROVED	DATE 7/1/03	CAD FILE NO. 102-0006AC1	DO NOT SCALE DWG	SIZE B	CAGE CODE 14949
NEXT ASSY		SCALE 4/1		DRAWING NO. 102-0006	REV. AC
				DATE: 7-12-68	SHEET 1 OF 3