



Technical Data

11.07.2022

Heat shrinkable tubing 2:1 on a reel
HIS-PACK

HIS-PACK-6.4/3.2

Article Number 300-30640



Material:

Polyolefin, cross-linked (PO-X)

Colour:

Black (BK)

Supplied Ø D min.:

6.4 mm

Recov. Ø d max.:

3.2 mm

Wall (WT):

0.60 mm

Shrink Ratio:

2:1

Longitudinal Change After Shrinkage:

+/-5%

Min. Shrink Temperature - °C:

+100 °C

Flammability:

self-extinguishing (except transparent), UL
224 VW-1 (except transparent)

Operating Temperature - °C:

-55 °C to +125 °C

Heat Shock Test:

4h/250°C

Behaviour at Heat Shock:

not dripping

Heat Aging Test:

168h/175°C

Dielectric Strength:

20 kV/mm

IEC 243

Insulation Class:

E (VDE 0530)

Tensile Strength:

17 MPa

Elongation at break:

800% (IEC 684 P2)

Water Absorption:

0.15 %

Specifications:

ANSI/UL 224, CSA-C22.1, CSA-C22.2
No.198.1

Test Method



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved