
PX0840/A3/1M00 Datasheet

Product Name // Overmoulded USB 3.0 Cable PX0840 Series USB Standard A Plug to Sealed A Plug 1m Cable

View Product Page





// Product Description:

- Pre-Wired Overmoulded USB 3.0 Cable
- Water and dustproof to IP68 when mated with compatible connector
- Standard USB 3.0 Type A plug to Sealed Standard USB 3.0 Type A plug
- 1m Cable Length
- PX0835 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with PX08 Standard USB 3.0 Series Panel Mount Connectors

// General Information:

Product Display Title:	Pre-Wired Overmoulded USB 3.0 Cable
Product Family:	Circular Data Connectors
Product Series:	Standard Buccaneer - USB
Body Colour:	Black
Body Material:	PVC
Cable Length:	1m
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	1A
Data Cable Type:	USB 3.0 Standard A Plug to Sealed A Plug
Diameter Over Coupling Ring Mm:	38.1mm
Flamability Rating:	UL94V-0
Ip Rating:	IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	0°C
Number Of Contacts:	9 Contacts
Rohs Compliant:	Yes
Voltage Max:	5V

// Product PDF Links

Standard Series USB connectors...

// Product 3D CAD Model Links

PX0840/A3/1M003D CAD Model

Have a question or project enquiry you'd like to talk to us about?

Click Here To Contact Us

Downloaded from Arrow.com.