

Representative Image

Catalog No. FCC-2A

Description: CABLE CLAMP 2IN NAT NYL SELF ADH

UPC No 5414363074670

Home > Wire & Cable Management > Ty-Rap > Nylon Cable Clips

Cable Clamp for Flat Cables, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 50.7mm (2 Inches), Width of 12.7mm (0.50 Inch), Height of 8.8mm (0.35 Inch) Minimum to 30.4mm (1.2 Inches) Maximum, M4 Countersunk Screw or Self-Adhesive Mounting Method

Descriptors

Category	Nylon Cable Clips

Specifications

Cable Type	Flat
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive/Screw
Number Of Cables	25

Classifications

Brand Name	Ty-Rap

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	50.7 mm
Length	2 inch
Width	12.7 mm
Width	0.5 inch
Height	8.8 mm
Height	0.35 inch
Type of fastening	Stick and screw
Material	Plastic
Material quality	Polyamide (PA)

by ABB

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Colour	Natural colour

Downloaded from Arrow.com.