




1.406

0.150

0.150

1.110

0.555

0.277

2X CLEARANCE HOLE
 $\phi .125$ - TOP MOUNT
 $\phi .208$ - BOTTOM MOUNT

4X R.05

RELAY

SOCKET

1 #4 FLAT WASHER;
CRES, PASSIVATE.

2 .112-40 HEX LOCK NUT,
CRES, PASSIVATE;
TORQUE TO 4±1 LB-IN.

3 #10 FLAT WASHER;
CRES, PASSIVATE.

4 .190-32 HEX LOCK NUT,
STEEL, CAD PLATE;
TORQUE TO 18±1 LB-IN.

5 #4 FLAT WASHER;
STEEL, CAD PLATE.


6 .112-40 HEX LOCK NUT,
STEEL CAD PLATE;
TORQUE TO 4±1 LB-IN.


MOUNTING STUD, FIXED;
CRES, PASSIVATE.

.093 MAX THK. PANEL.

NOTES:

1. PART DESIGNED PER STANDARDS AND FUNCTIONAL REQUIREMENTS OF MIL-PRF-12883.
2. MATERIALS:
HOUSING - POLYETHERIMIDE, COLOR: BLUE-GREEN.
GROMMET - SILICONE RUBBER, COLOR: RED.
3. PART ACCEPTS EIGHT P/N CNS127900 SOCKET CONTACTS;
SUPPLIED IN SEPARATE CONTAINER WITHIN UNIT PACKAGE.
4. MOUNTING HARDWARE SUPPLIED IN SEPARATE BAG
WITHIN UNIT PACKAGE.
5. CONTACT INSTALLATION TOOLS:
CRIMP TOOL - M22520/1-01
POSITIONER - M22520/1-02
INS/REM TOOL - M81969/14-03



DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±01 .XXX ±005 ANGLES ±2°	PROJECTION 	SPECIFICATION DRAWING			TITLE RELAY SOCKET 2 POLE, 10 AMP SIZE 16/20, 8 POS		
			ENGR A. PATRIE 12/21/98					
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA	CHKD			SIZE B	DWG NO. RSE116512		REV J
		APPD			CODE: 58982		SCALE: 2X	SHEET 1 OF 1