


OGA DIAGONAL: 7.94 [201.60]
 VA DIAGONAL: 7.13 [181.06]
 PA DIAGONAL: 6.75 [171.51]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9131-203	98-0003-2699-5	FFC	4.27" [108.46]	AG500	23655
17-9131-221	98-0003-2701-9	SER	4.27" [108.46]	AG500	23655
17-9131-206	98-0003-3041-9	NOV	SEE DWG	AG500	23655
17-9131-218	98-0003-3125-0	USB R	4.27" [108.46]	AG500	23655



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 141±10%
2. NICOMATIC HOUSING P/N: OLO5
 NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
 HOUSING ORIENTED WITH LATCH DOWN

UNITS	INCHES [MM]	3M TOUCH SYSTEMS METHUEN, MA USA
TOLERANCES UNLESS OTHERWISE SPECIFIED		
.X	± .03 [.76]	
.XX	± .015 [.38]	
.XXX	± .015 [.38]	
ANGLES	± 1°	
THIRD ANGLE PROJECTION		
DO NOT SCALE DRAWING		
SCALE	1 = 1	

J	REVISED PER CO 036256	4/13	SB
H	REVISED PER CO 033533	2/12	SB
G	REVISED PER CO 033709	10/11	SB
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING SCT32NN 7.13"			
DRAWN A.OUELETTE 05/01/06		SHEET 1 OF 1	
C		31826-MKT	
J			