

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130143-0310

Status:

Active

Overview:

Watertite® Wet-Location Wiring Solutions

Description:

Watertite® UV Resistant Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L14-30, 125V/250V, Black

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General	
Product Family	Wiring Devices
Series	130143
Comments	125V and 250V
IP Rating	IP67
NEMA Configuration	NEMA L14-30
Overview	Watertite® Wet-Location Wiring Solutions
Product Literature Order No	987650-8067
Product Name	Watertite®
Receptacle Type	N/A
Specialty	N/A
Type	Cordset
UPC	78678812799
Woodhead	Yes
Physical	
Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	Yes
Poles	3-pole/4-wire
Electrical	
Cord Type	10/4 SOOW
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V / 250V
Material Info	
Old Part Number	28W74A104BLK



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130143Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION