

Part #

GO!

Keyword

GO!

[Home](#) [About](#) [Distributor Locator](#) [FAQs](#) [Contact](#)

## NTE Electronic Components

AC-DC Adapters

**NEW ITEMS!**

Binding Posts & Banana  
Sockets **NEW PRODUCT!**

Bulbs **NEW PRODUCT!**

Cable/Wire-Ties/  
Bundle Management  
**NEW ITEMS!**

Capacitors

Circuit Protection

Clips/Test Leads

Fans

Fuses

Heat Shrink Tubing

LED Strips/EL Wire/  
LED Lamps

Optoelectronic Devices

Pots/Trimmers/  
Knobs/Dials

Relays/Contactors

Resistors

Semiconductors

Solder Wick

Switches **NEW TYPES!**

Terminal Blocks

Terminals &amp; Connectors

Wire

## ECG Consumer/ Commercial Products

Antenna Rotors

Chemicals

Heat Guns

Infrared Thermometer

**Solder Irons/De-Soldering  
Tools NEW TYPES!**

Surge Protectors

Test Equipment

Wireless Security &  
Inspection Cameras

## Master Distributed Lines

Amphenol RF /  
Connex: Connectors

CML: Optoelectronic  
Products

Chemtronics **NEW LINE!**

Coast: LED Flashlights

Kester Solder Products





Plato: Soldering Tools,  
Tips, & Accessories

Samlex: Power  
Inverters

SureHold: Glues and  
Adhesives

Techspray: Chemicals

## Soldering Irons, Corded Electric Soldering Stations

	Model No.	Wattage	Description	Available Tips
	J-2040SS	20/40	<b>20/40 Watt Dual Heat Switchable Corded Soldering Station.</b> UL & C UL approved, switchable 20/40 watt soldering iron with ON/OFF switch. Space-saving all-in-one design has coil spring iron holder and a built-in sponge pad for quick tip cleaning.	<a href="#">JT-010</a> <a href="#">JT-013</a>
	J-SSA-1	75	<b>Analog 75w Industrial Soldering Station, ESD Safe.</b> Rapid heating, fast temperature compensation, stable temperature control. Adjustable temperature range: 200°C to 450°C / 392°F to 842°F +-10%.	<a href="#">JT-208</a> thru <a href="#">JT-212</a>
	J-SSA-2	50	<b>Analog 50w Soldering Station.</b> Advanced temperature control circuitry allows for precise control, includes built-in soldering stand with sponge and flux, includes spooled solder holder. Adjustable temperature range: 200°C to 500°C / 392°F to 932°F +-10%.	<a href="#">JT-205</a> <a href="#">JT-206</a>
	J-SSD-1	75	<b>Digital 75w Industrial Soldering Station, ESD Safe.</b> Rapid preheating, fast temperature compensation, LED digital temperature display in centigrade shows actual iron temperature. Adjustable temperature range: 200°C to 450°C (equivalent 392°F to 842°F) +-10%.	<a href="#">JT-208</a> thru <a href="#">JT-212</a>

## ECG Solder & Heat Products Links

### Soldering Irons & Torches

- Butane Powered
  - Replacement Tips & Butane
- Corded Electric
  - Replacement Tips
- Battery Operated
  - Replacement Tips
- Soldering Stations
  - Replacement Tips

### De-Soldering Tools

- Electric and Mechanical
  - Replacement Tips

### Soldering Aids

- Stands
- Tip Cleaners
- Wire Balls
- Helping Hands

### Related Documents

[Home](#)  
[Distributor Locator](#)  
[FAQs](#)
[About](#)  
[Environmental](#)  
[QUICKCross Download](#)
[Contact](#)  
[Manufacturing Disclaimer](#)
[Sitemap](#)  
[Privacy Policy](#)


Follow NTE on  
Facebook and Twitter