



Part Number : [1301050041](#)
Product Description : Watertite Wet Location
Incandescent Hand Lamp, 100W with LOVOLT In-line
Transformer TEFLON Globe with Screw Release
TEFLON Guard, Cord Type 14/2 SOOW, 7.62m (25.0')
Cord Length
Series Number : 130105
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1625-12A



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer TEFLON Globe with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862504

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/2 SOOW

Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Teflon*
Material - Guard	N/A
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 23, 2025