






PART NUMBER	PACK	HOOD SIZE
8655AZETIAI1KLF	KIT	09








NOTES: (FOR EVERY SIZES)
1- OPERATING TEMPERATURE: -40°C TO +120°C
2- INDIVIDUAL KITS SEALED IN PLASTIC COVER
IN UNASSEMBLED FORM.
BOM AS SHOWN IN TABLE

RoHS INFORMATION:
- THE LF PRODUCT MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS+22-009
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS

ITEM NO.	QTY.	PART DESCRIPTION
1	1	DTPK09-UPPER COVER
2	1	DTPK09-LOWER COVER
3	2	M3X11.5 SCREW
4	1	D45ZK-D2 GROMMET SET
5	2	UNC 4-40X47 JACKSCREW
6	2	M3 NUT


spec ref	-	dr	Dipu Joseph	2020/09/18	projection	mm	size	A3	scale	3:2
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/11/17	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Wollin, Severi	2020/11/13	product family	-	rel level	Released	rev	A
ISO 1302	angular	0°	±2°	Amphenol FCi	DSUB METALIZED HOOD	cat. no.	-	Product - Customer Drw	sheet 1 of 4	

PART NUMBER	PACK	HOOD SIZE
8655AZATIAI1KLF	KIT	15








GROMMET SET

ITEM NO.	QTY.	PART DESCRIPTION
1	1	DTPK15-UPPER COVER
2	1	DTPK15-LOWER COVER
3	2	M3X11.5 SCREW
4	1	D45ZK-D2 GROMMET SET
5	2	UNC 4-40X47 JACKSCREW
6	2	M3 NUT

spec ref -		dr Dipu Joseph		2020/09/18			size A3	scale 3:2	
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng Detouillon, Da	2020/11/17			ecn no -		
			chr -	-			rel level Released		
			appr Wollin, Severi	2020/11/13	product family -				
surface  ISO 1302	linear	0.X	±0.3	Amphenol FCi	title DSUB METALIZED HOOD	dwg no 8655AZxx1A11KLF	rev A		
		0.XX	±0.10						
		0.XXX	±0.005						
		angular	0°	±2°	cat. no. -	Product - Customer Drw		sheet 2 of 4	

PART NUMBER	PACK	HOOD SIZE
8655AZBTIAI1KLF	KIT	25








GROMMET SET

ITEM NO.	QTY.	PART DESCRIPTION
1	1	DTPK25-UPPER COVER
2	1	DTPK25-LOWER COVER
3	2	M3X11.5 SCREW
4	1	D45ZK-D2 GROMMET SET
5	2	UNC 4-40X47 JACKSCREW
6	2	M3 NUT

spec ref	-	dr	Dipu Joseph	2020/09/18	projection	mm	size	A3	scale	1:1
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/11/17	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Wollin, Severi	2020/11/13	product family	-	rel level	Released	rev	A
ISO 1302	angular	0°	±2°	Amphenol FCi	DSUB METALIZED HOOD	cat. no.	-	Product - Customer Drw	sheet 3 of 4	

PART NUMBER	PACK	HOOD SIZE
8655AZCTIAI1KLF	KIT	37



GROMMET SET

ITEM NO.	QTY.	PART DESCRIPTION
1	1	DTPK37-UPPER COVER
2	1	DTPK37-LOWER COVER
3	4	M3X11.5 SCREW
4	1	D45ZK-D2 GROMMET SET
5	2	UNC 4-40X47 JACKSCREW
6	4	M3 NUT

spec ref	-	dr	Dipu Joseph	2020/09/18	projection	mm	size	A3	scale	1:1
tolerance std	ISO 406 ISO 1101	eng	Detouillon, Da	2020/11/17	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Wollin, Severi	2020/11/13	product family	-	rel level	Released	rev	A
ISO 1302	angular	0°	±2°	Amphenol FCi	DSUB METALIZED HOOD	cat. no.	-	Product - Customer Drw	sheet 4 of 4	