



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads

plugs
sockets
▶ 2 mm system
▶ 2 mm safety system
▶ 4 mm system
▶ 4 mm safety system

sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ sockets ▶ sockets ▶ SEB 2620 F6,3

SEB 2620 F6,3

datasheet for SEB 2620 F6,3
article number: 972356101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 972 356-101
description:	Safety built-in socket, 4 mm diameter, contact-protected, with 6.3 x 0.8 tab connector complying with DIN 46 244, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Installation hole: 12.2 mm diameter, Tightening torque: 50 Ncm, Accessory: assembly tool MW SEB
typ:	SEB 2620 F6,3 rot/red
system:	4mm safety system
order number:	972 356-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of contact:	4 mm socket (unsprung)
type of termination:	flat connector 6.3 x 0.8 mm
rated voltage:	AC/DC 1000 V
rated current:	32 A
Please consider derating curve!	
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	gold
housing material:	PA
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-40 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	
	